



Straight Blade Devices, Male Plug, Valise Series, Hospital Grade, Straight, 2-Pole 3-Wire Grounding, 20A 250V, 6- 20P, White, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL8464V](#)



Straight Blade Male Plug, Valise Series, Hospital Grade, Straight, 2-Pole 3-Wire Grounding, 20A 250V, 6- 20P.

Features

- Hinged one piece body design for easy assembly
- Powerful, offsetting cord grips clamp on individual conductors

Application

Hospital Grade

General

Color	<ul style="list-style-type: none"> • White • Blanc
Cord Range	0.300"-0.660" (7.6-16.8)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Insulation	Insulated Body
Item Type	Valise Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2000V AC minimum • Environmental - Flammability - UL 94 HB • Environmental - IP Suitability - IP20 • Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device

Dimensions

Dimensions	1.88 in x 1.5 in x 1.13 in
Display Size	Standard
Height	1.13 in
Length	1.88 in
Weight	0.1 lb
Width	1.5 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	250 V
Voltage Rating Description	250 V

Conductor Related

Conductor Range	#18AWG to #12AWG
Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified to C22.2 No 42 File 280C • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E1706
----------------------	---

Nema Rating	6-20P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK L-11 Catalog Page](#)
[Catalog Page - WDK A-36 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Installation Manuals - WIRING_PD1237_INSTALLINST](#)

- Mechanical - Terminal Accommodation - #18-#12 AWG stranded copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Series	Hospital Grade
Style	Valise
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	<ul style="list-style-type: none">• Plug• Plug
UPC	783585016375



A proud member of the Hubbell Family.