

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 8 Outlet with Telephone/Fax, 150 Joules, 6' Cord, Office White

By Hubbell Wiring Device-Kellems
Catalog # [HBL8ESPS1050M](#)



Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A
125V, 8 Outlet with Telephone/Fax, 150 Joules, 6' Cord, Office
White.

Features

- Four outlet, 1050 joule SPD features a black housing
- 6 foot cord, 90 degree plug, and two USB ports for charging

General

Catalog Number	HBL8ESPS1050M
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Indicator
Item Type	Surge Protection Plug Strips
Material	Non-Metallic
Material - Mounting Hardware	Portable
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Performance	Electrical - Max Surge Current - 19.5kA Electrical - Max. Operating Voltage - 130 Electrical - Operating Frequency - 50/60Hz Environmental - Operating Temperature - -40°F to 160°F (-40°C to 70°C)
Response Time	5
UPC	783585120621

Dimensions

Display Size	1050 Joules
--------------	-------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 VAC

Logistics

Carton Quantity	20
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBL8ESPS1050M AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2380_INSTALLINST](#)
[Sales Drawings - WDK_HBL8ESPS1050M_DRAWING_PDF](#)
[Warranty - Surge Plug Strips](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_CA-HBL8ESPS1050M-SPEC-EN | REV 6/2024