



Straight Blade Devices, Receptacles, RTP, Industrial Grade, 2-Pole 3-Wire Grounding, 30A 250V, 6-30R, Black, Single Pack.

By Hubbell Wiring Device-Kellems
Catalog # [HBL9330](#)



Straight Blade Single Flush Receptacle 30A, 2-Pole, 3-Wire Grounding, 250V, 6-30R.

Features

- Sequenced contacts assure protection
- Catalog number, ratings and certifications molded in face
- One piece design power and ground contacts
- Catalogue number, ratings and certifications molded in face

Application

Heavy Duty

General

Color	Noir
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 V-0 • Environmental - IP Suitability - IP20 • Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #12 AWG through #4 AWG copper wire only
-------------	--

Dimensions

Dimensions	3.28 in x 2.25 in x 2.23 in
Display Size	Standard Sized Product
Height	2.23 in
Length	3.28 in
Weight	0.4 lb
Width	2.25 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	7500 W

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#12 AWG to #4 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified • NEMA® WD-6 Compliant • UL Listed File E2186
Nema Rating	6-30R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK N-18](#) [Catalog Page - WDK A-45](#) [Catalog Page - WDK Catalog Full 2023](#)
[Engineering Drawing - HBL9330 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1185_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Pulp & Paper Solutions](#)

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

[Sales Drawings - WDK_HBL9330_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Insulgrip Twist-Lock and Straight Blade Devices](#)

Series	Extra Heavy Duty
Style	Grounding
Type	<ul style="list-style-type: none">• Receptacle• Receptacle
UPC	783585015231



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL9330-SPEC-EN | REV 1/2024