

PlugTrak, Aluminum, Tamper Resistant, 20A Circuit, 5 Receptacle, 5' Aluminum



By Hubbell Wiring Device-Kellems
Catalog # [HBLALU24GB512](#)

PlugTrak, Aluminum, Tamper Resistant, 20A Circuit, 5 Receptacle, 5' Aluminum

Features

- Multiple spacing configurations
- Satin anodized scratch resistant finish
- Hubbell designed and manufactured single receptacle
- Insulation displacement wiring provides superior wire retention

Performance

- Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R
- Mechanical - Wire - #12 AWG Stranded Copper

General

Catalog Number	HBLALU24GB512
EU RoHS Indicator	Contact Manufacturer
Item Type	Aluminum Pre-Wired PlugTrak
Number of Receptacles	5
Series	Aluminum
Specifications	• Circuits - Single • Material - Anodized Aluminum • Number of Receptacles - 5 Singles • PlugTrak Length - 5 Foot • Receptacle Face - Thermoplastic • Receptacle Spacing - 12 Inch
Style	Standard
Type	Single Circuit
UPC	783585113364

Dimensions

Length 5 ft

Electrical Ratings

Current / Amperage Rating 15 A
Voltage Rating 125 VAC

Conductor Related

Wire Size #12 AWG THHN

Certifications And Compliance

Industry Standard(s)

- CSA Standard C22.2 no. 62
- E253976 /E253830 /E253833
- UL Standard UL 5

Logistics

Carton Quantity 2

Product Assets

[Catalog Page - WDK S-36](#) [Catalog Page - WDK S-51](#) [Catalog Page - WDK S-51](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBLALU24GB512 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2283_INSTALLINST](#)
[Sales Drawings - WDK_HBLALU24GB_DRAWING_PDF](#)
[Specifications - Wiring HBLALU24GB512 Specification Sheet](#)
[Specifications - HBLALU24GB512 Specification Sheet French](#)
[Specifications - HBLALU24GB512 Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)