

# Cord and Cable Reels, Commercial Cord Reel, 40', 15A 125V with Triple Tap, Yellow

By Hubbell Wiring Device-Kellems  
Catalog # [HBLC40123TT](#)



Cord and Cable Reels, Commercial Cord Reel, 40', 15A 125V with Triple Tap, Yellow

## Features

- Removable bracket allows reel to be dis-engaged from mount
- Durable light weight non-metallic housing
- 40 Ft. of 12/3 cord for greater current carrying capacity

## Application

Bench, Ceiling and Wall Mounted

## Performance

Environment - Operations - Dry, indoor, non-hazardous locations

## General

Base Type	Optional
Cable Length	40 Ft
Cable Type	#12/3 SJTW
Catalog Number	HBLC40123TT
Construction	Non-metallic
Duty	Heavy Duty
EU RoHS Indicator	No
Item Type	Reel with Triple Tap
Series	Commercial
Specifications	<ul style="list-style-type: none"><li>• Cable Feet (m) - 40 (12.2)</li><li>• Cable Type - 12/3 SJTW</li><li>• Watts (Max) - 1875 W</li><li>• Weight Lbs. (kg) - 9.0 (4.1)</li></ul>
Style	Three Outlets
Type	Reel With Triple Tap
UPC	783585524849

## Dimensions

Cable Length Active	480
Cable Length Inactive	24
Reel Frame Dimension	Steel

## Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

## Conductor Related

Cable Specification	12/3 SJTW
Feeder Cord	12/3 SJTW
Nema Color	Black

## Certifications And Compliance

Industry Standard(s)	UL 355 Listed
----------------------	---------------

## Logistics

Carton Quantity	1
Pallet Quantity	70

## Product Assets

[BIM - Speciality\\_Equipment-Cord\\_Reel-Hubbell\\_Wiring-System\\_K5-HBLC40123TT](#)  
[Catalog Page - WDK J-7 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - HBLC40123TT AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2147\\_INSTALLINST](#)  
[Literature - Cord Reels](#)  
[Literature - Safety Product Guide](#)  
[Literature - Education Application Guide](#)  
[Literature - Safety Product Guide](#)  
[Literature - 2017 NEC® Code Changes Guide](#)  
[Sales Drawings - WDK\\_HBLC40123\\_DRAWING\\_PDF](#)  
[Specifications - HBLC40123TT Specification Sheet English](#)  
[Specifications - WIRING\\_HBLC40123TT\\_spec](#)  
[Specifications - HBLC40123TT Specification Sheet French](#)  
[Warranty - Industrial & Commercial Products](#)