

Industrial Grade, Motor Disconnect, Unfused Switch, Non-Metallic Sloped Version Replacement Cover for 30A With inTOUCH Installation Free LED Phase Indication and Jog - HBLDS30 and HBLDS30T Series

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS30RCPJ](#)

Industrial Grade, Motor Disconnect, Unfused Switch, Non-Metallic Replacement Cover for 30A With inTOUCH Installation Free LED Phase Indication and Jog, HBLDS30 and HBLDS30T Series

Features

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- Rounded sloped top enclosure supports best practices in hygienic design by shedding dirt and debris
- IP69k and Type 4X,12K water ingress protection
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Certified by NSF for hygiene in food processing applications
- Product rating are permanently laser-marked and will not wash off
- Six highly visible integral phase identification LEDs for use on 3 Phase Y or Delta systems provide secondary means of visual confirmation of make/break on all phases

Application

Heavy Duty Industrial and/or Washdown

Specifications

Industry Standard(s)	cULus Listed
Environmental Conditions	Indoor and Outdoor

Dimensions

Weight	1.1 lb.
--------	---------

General



Specifications

Color
Style
Ingress Protection
UPC
Type
Material - Mounting Hardware
Enclosure Type
Series

- Enclosure Gasket - Neoprene
 - Handle - Valox®
 - Shaft (Unfused) - Valox®
 - Top - Valox®
- Gray
Replacement Cover
IP69k, NEMA Type 4X, 12
783585763170
Accessories
Stainless Steel Screw Mounting
IP69k and UL Type 4X, 12
Non-Fused

Logistics

Pallet Quantity	360
Carton Quantity	1

Operational

Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Without Impact Maximum continuous 75°C and minimum -40 °C

Product Assets

[Catalog Page \[English\]](#)
[Installation Manual \[English\]](#)