

Industrial Grade, MotorQuick Disconnect
Switches, Unfused Switch, Three Pole, 30A
600V AC, Screw Terminals, With 5' Pre-
Wired Female Cable

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS3MQ5](#)

Switches and Lighting Controls, Industrial Grade, MotorQuick
Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC,
Screw Terminals, Gray, With 5' Pre-Wired Female Cable

Features

- High Impact Valox® Enclosure
- Lockable Handle to meet OSHA Lockout/Tagout Regulations
- Type 4X Enclosure

Performance

Electrical - Dielectric Voltage - 2,200V AC minimum for 1 minute,
Electrical - Electrical Life - 6,000 cycles with load, Electrical -
Max. Working Voltage - 600V AC RMS, Environmental -
Flammability - UL94-5VA and V0 Classification, Environmental -
Operating Temperature - Max. continuous 75°C, Min. continuous
-40°C, Mechanical - Impact Resistance - UL746C, Mechanical -
Mechanical Life - 10,000 minimum cycles, Mechanical - Terminal
Accommodations - 30A, #14 AWG Min. - #10 AWG Max,
Mechanical - Terminal Torque - 30A, 20 inch pounds

Specifications

Industry Standard(s)	• Listed to UL 2238 and UL 50E • UL 508, Industrial Control Equipment File #E36355
Environmental Conditions	Indoor and Outdoor
EU RoHS Indicator	No

Conductor

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

Current

Amperage Rating	30 A
Wattage	18000
Connectivity	Pre-Wired
Dielectric Strength	2,200V AC minimum for 1 minute
Phase	Three Phase
Current Rating	30 A

Dimensions

Weight	4.9 lb.
--------	---------



Height	4.12 in
Width	6 in
Length	8.5 in
Display Size	Standard Sized Product
Dimensions	8.5 in x 6 in x 4.12 in

Force Related

Load Capacity	Inductive
---------------	-----------

General

Specifications	• Contact Carrier - Nylon 6/6, white • Contact Materials - Brass pins • Contact Plating - Hard gold over palladium/nickel • Coupling Hardware - Nickel plated brass • Overmold Material - Glass filled polyurethane, gray
Ingress Protection	IP67
UPC	783585310954
Type	Disconnect Switches
Material - Mounting Hardware	Screw Mounting
Enclosure Type	Type 4X
Series	MotorQuick/LINKOSITY

Operational

Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Horsepower - Maximum	15

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)