

Disconnect Switches, 30A 600V AC,
3-Pole, Unfused, Jog Control, NEMA
4X, with LED Indicator

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS3PJ](#)

Disconnect Switch 30A 600V AC, 3-Pole,Unfused, Jog Control,
NEMA 4X with LED Indicator

Features

- Six highly visible integral phase identification LEDs for use on 3 Phase Y system
- LEDs provide secondary means of visual confirmation of make/break on all phases
- Cover cannot be removed with switch in the “ON” position
- Verification of opening of load side contacts
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements

Application

LED Indictor / Jog Switch / Labelless

General

Catalog Number	HBLDS3PJ
EU RoHS Indicator	Contact Manufacturer
Enclosure Type	Type 4X, IP69k
Series	Non-Fused
Style	Heavy Duty
Type	Disconnect Switches
UPC	783585365145

Electrical Ratings



Amperage Rating	30 A
Current / Amperage Rating	30 A

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Catalog Page - WDK F-5 Catalog Page](#)
- [Catalog Page - WDK F-11 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBLDS3PJ AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2790_PD1782_INSTALLINST](#)
- [Literature - Safety Product Guide](#)
- [Literature - Circuit-Lock® Disconnects with LED Indicators](#)
- [Literature - Circuit-Lock® Motor Disconnects](#)
- [Literature - Circuit-Lock® 30A Disconnects with LED Indicators](#)
- [Sales Drawings - WDK_HBLDS3PJ_DRAWING_PDF](#)
- [Specifications - HBLDS3PJ Specification Sheet French](#)
- [Specifications - Wiring HBLDS3PJ Specification Sheet](#)
- [Specifications - HBLDS3PJ Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - InSight Motor Disconnects](#)
- [Video - InSight Motor Disconnects](#)