

Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Replacement Switch, Three Pole, For 30A Black

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS3RS](#)

Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Replacement Switch, Three Pole, For 30A Black

Features

- Industrial Grade
- Disconnect Switches
- Replacement Switch
- Three Pole

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current voltage, Electrical - Dielectric Voltage - Withstands 3,000V Min, Electrical - Max. Working Voltage - 600V RMS, Electrical - Operations - Mechanical 10,000 cycles, Electrical 6,000 cycles, Environmental - Flammability - Meets UL 94V0 material classification, Environmental - Moisture Resistance - IP66 suitability, Environmental - Operating Temperature - Maximum continuous +75°C Minimum continuous -40°C, Environmental - UV Resistance - All exposed materials are UV stabilized, Mechanical - Impact Resistance - In accordance with UL 746C, Mechanical - Mounting - External full adjustable feet, Mechanical - Product Identification - Identification and ratings are part of the external label and receptacle face, Mechanical - Terminal Identification - In accordance with UL, CSA

Specifications

Standards - RoHS Compliance Status	CM
EU RoHS Indicator	No
Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified TYPE 4, 4X and TYPE 12K Enclosure Rating • Listed to UL Standard

Current



Amperage Rating	30 A
Dielectric Strength	Withstands 3,000V minimum
Current / Amperage Rating	30 A

Dimensions

Weight	0.4 lb.
--------	---------

General

Style	Replacement Switches
Series	<ul style="list-style-type: none"> • Non-Fused • Fused
UPC	783585955179
Type	Accessories
Item Type	Mechanical Interlock Replacement Switch

Logistics

Pallet Quantity	1900
Carton Quantity	20

Operational

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
-----------------------	--

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[French\]](#)