

Switches and Motor Controls, Industrial  
Grade, Disconnect Switches, Unfused  
Switch, Three Pole, 30A 600V AC, Stainless  
Steel, NEMA 4X Enclosure

By Hubbell Wiring Device-Kellems  
Catalog # [HBLDS3SSAC](#)

Switches and Motor Controls, Industrial Grade, Disconnect  
Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw  
Terminals, Stainless Steel, NEMA 4X Enclosure, With Aux Contact

Features

- Formed in nonporous 304 stainless steel
- IP69k and Type 4X,12K water ingress protection
- Certified by NSF for hygiene in food processing applications
- Highly visible red handle which meets OSHA Lockout/Tagout capabilities
- Accepts up to 2 Auxiliary contacts

Application

Labelless

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage, Electrical - Dielectric Voltage - Withstands 3000V AC minimum, Electrical - Max. Working Voltage - 600V AC RMS, Environmental - Flammability - UL94-5VA and V0 Classification, Environmental - Operating Temperature - Max Continuous 75°C,Min Continuous -40°C w/o impact, Environmental - UV Resistance - All materials are UV stabilized, Mechanical - Impact Resistance - In accordance with UL 746C, Mechanical - Mounting - Stainless Steel - Feet are fixed, Mechanical - Product Identification - Identification and ratings are part of external label, Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

Specifications

|                             |           |
|-----------------------------|-----------|
| Standards - RoHS Compliance | CM        |
| Status                      |           |
| EU RoHS Indicator           | Yes       |
| Industry Standard(s)        | UL Listed |

Configuration

|                 |                |
|-----------------|----------------|
| Mounting Method | Feet are fixed |
|-----------------|----------------|

Current

|                     |                             |
|---------------------|-----------------------------|
| Amperage Rating     | 30 A                        |
| Dielectric Strength | Withstands 3000V AC minimum |



|                           |             |
|---------------------------|-------------|
| Current Rating            | 30 A        |
| Phase                     | Three Phase |
| Current / Amperage Rating | 30 A        |

Dimensions

|            |                             |
|------------|-----------------------------|
| Length     | 8.38 in                     |
| Height     | 5.39 in                     |
| Width      | 4.87 in                     |
| Dimensions | 8.38 in x 4.87 in x 5.39 in |

General

|                    |                                                                                                                                                                                                                                                   |
|--------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Style              | Heavy Duty                                                                                                                                                                                                                                        |
| Ingress Protection | IP69K                                                                                                                                                                                                                                             |
| Enclosure Type     | Type 4X, IP69k                                                                                                                                                                                                                                    |
| Series             | Non-Fused                                                                                                                                                                                                                                         |
| Specifications     | <ul style="list-style-type: none"><li>• Base - #14 Gauge Type 304 Stainless Steel</li><li>• Enclosure Gasket - Neoprene</li><li>• Handle - Valox®</li><li>• Shaft (Unfused) - Valox®</li><li>• Top - #14 Gauge Type 304 Stainless Steel</li></ul> |
| UPC                | 783585242743                                                                                                                                                                                                                                      |
| Type               | Disconnect Switches                                                                                                                                                                                                                               |

Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|

Operational

|                       |                                                          |
|-----------------------|----------------------------------------------------------|
| Operating Temperature | Maximum continuous 75°C and minimum -40°C without Impact |
|-----------------------|----------------------------------------------------------|

Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)  
[Catalog Page \[English\]](#)  
[Installation Manual \[Spanish, French, English\]](#)