



Wiring Device-Kellems

Disconnect Switches, Sloped Enclosure, 30A 600V AC, Non-Fused, NEMA 4X, Stainless Steel

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS3SSR](#)



Disconnect Switches, Sloped Enclosure, 30A 600V AC, Non-Fused, NEMA 4X, Stainless Steel.

Features

- Formed in nonporous 304 stainless steel
- IP69k and Type 4X,12K water ingress protection
- Certified by NSF for hygiene in food processing applications
- Highly visible red handle which meets OSHA Lockout/Tagout capabilities
- Accepts up to 2 Auxiliary contacts

Application

Labelless

General

| | |
|-----------------------|---|
| Color | <ul style="list-style-type: none"> • Steel • Acier |
| EU RoHS Indicator | |
| Enclosure Type | Contact Manufacturer Type 4X, IP69k |
| Mounting Method | Feet are fixed |
| Operating Temperature | Maximum continuous 75°C and minimum -40°C without Impact |
| Performance | <ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage • Electrical - Dielectric Voltage - Withstands 3000V AC minimum • Electrical - Max. Working Voltage - 600V AC RMS • Environmental - Flammability - UL94-5VA and V0 Classification • Environmental - Operating Temperature - Max Continuous 75°C,Min Continuous -40°C w/o impact • Environmental - UV Resistance - All materials are UV stabilized • Mechanical - Impact Resistance - In accordance with UL 746C • Mechanical - Mounting - |

Dimensions

| | |
|------------|----------------------------|
| Dimensions | 8.6 in x 5.41 in x 4.92 in |
| Height | 4.92 in |
| Length | 8.6 in |
| Width | 5.41 in |

Electrical Ratings

| | |
|---------------------------|-----------------------------|
| Amperage Rating | 30 A |
| Current / Amperage Rating | 30 A |
| Current Rating | 30 A |
| Dielectric Strength | Withstands 3000V AC minimum |

Logistics

| | |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|

Product Assets

- [Catalog Page - WDK F-7 Catalog Page](#)
- [Catalog Page - WDK F-17 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBLDS3SSR AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2665_INSTALLINST](#)
- [Literature - Labelless Disconnects](#)
- [Literature - Food Processing Guide](#)
- [Literature - Healthcare Application Guide](#)
- [Literature - Industrial Solutions](#)
- [Literature - Circuit-Lock® Motor Disconnects](#)
- [Literature - Safety Product Guide](#)
- [Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
- [Sales Drawings - M12746](#)
- [Warranty - Industrial & Commercial Products](#)

Mechanical - Mounting
Stainless Steel - Feet are
fixed

- Mechanical - Product
Identification -
Identification and ratings
are part of external label
- Mechanical - Terminal
Identification - In
accordance with UL, CSA
and international
conventions

Series

Non-Fused

Style

Heavy Duty

Type

- Disconnect Switches
- Disconnect Switches

UPC

783585541549



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBLDS3SSR-SPEC-EN | REV 1/2024