

White Industrial Reel with Black
Portable Outlet Box and (1) 20A
Duplex Receptacle, UL Type 1, 25
Ft, #12/3 SJO, 20 A, 125 VAC

By Hubbell Wiring Device-Kellems
Catalog # [HBLI25123R20M1](#)



White Industrial Reel with Black Portable Outlet Box and (1) 20A
Duplex Receptacle, UL Type 1, 25 Ft, #12/3 SJO, 20 A, 125 VAC

Features

- Durable, Corrosion Resistant Cast Aluminum Construction
- UL Type 1
- Multi-Position Guide Arm can be mounted in two different positions
- Positive Latch mechanism automatically maintains desired cord length
- Ratchet Lock can be disengaged in field for constant tension applications

Application

Industrial

General

Cable Length	25 Ft
Cable Type	#12/3 SJO
Catalog Number	HBLI25123R20M1
EU RoHS Indicator	Contact Manufacturer
Series	inREACH
Style	Two Outlets
Type	Reel With Duplex Receptacle(s)
UPC	783585669779

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating	125 VAC

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBLI25123R20M1 AutoCAD Drawing](#)
- [Installation Manuals - PD3071](#)
- [Installation Manuals - PD2847](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_HBLI45123R2_DRAWING_PDF](#)
- [Specifications - HBLI25123R20M1 Specification Sheet French](#)
- [Specifications - Wiring HBLI25123R20M1 Specification Sheet](#)
- [Specifications - HBLI25123R20M1 Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - inREACH Cord Reel Drop Ceiling Enclosure](#)