

Temporary Lighting Products, High
Bay LED Light, 120W

By Hubbell Wiring Device-Kellems
Catalog # [HBLLEDHB120](#)

Temporary Lighting Products, High Bay LED Light, 120W

Features

- Easy, portable LED light fixture
- 120% LED efficiency
- Wire cage and Polycarbonate lens design for durability

Performance

- Electrical - Lamp life - 50,000 hours
- Mechanical - Height - 16"
- Width - 10" - Depth

General

Catalog Number	HBLLEDHB120
EU RoHS Indicator	Contact Manufacturer
Series	High Bay Light
Specifications	<ul style="list-style-type: none">• Light Type - LED• Plug type - NEMA 5-15P
Type	High Bay LED Light With Wire Guard
UPC	783585468976

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Catalog Page - WDK H-16 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Safety Product Guide](#)
- [Literature - Temporary Industrial Lighting](#)
- [Specifications - HBLLEDHB120 Specification Sheet](#)
- [Specifications - HBLLEDHB120 Specification Sheet French](#)
- [Specifications - Wiring HBLLEDHB120 Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Temporary Industrial Lighting](#)
- [Video - Temporary Industrial Lighting](#)

