

Temporary Lighting Products, 28W
Light String, With In-Line Switch,
2928 Lumen Output

By Hubbell Wiring Device-Kellems
Catalog # [HBLLS2834](#)

Temporary Lighting Products, 28W Light String, With In-Line
Switch, 2928 Lumen Output

Features

- Inline on/off switch for ease of operation
- Extra durable polycarbonate outer tube
- Diffuser protects user’s eyes from bright light

Performance

- Electrical - Lamp Life - 50000
- Electrical - Light Angle Degree - 130
- Electrical - Light Color - 4700-5200 K
- Electrical - Lumen Output - 2928
- Electrical - Rating - 15A 125V
- Electrical - Watts - 28
- Mechanical - Cord Length - 6 ft.
- Mechanical - Cord Type - 16 AWG SJTOW

General

Catalog Number	HBLLS2834
EU RoHS Indicator	Contact Manufacturer
Series	Stringer Lights
Specifications	• Length - 34.25 • Light Type - LED • Plug Type - NEMA 5-15P • Width - 2.625



Type	LED Stringer Lights
UPC	783585467283

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

Certifications And Compliance

Industry Standard(s)	• CSA • ETL • UL
----------------------	--

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Safety Product Guide](#)
- [Literature - Temporary Industrial Lighting](#)
- [Literature - Emergency Preparedness for Healthcare](#)
- [Specifications - Wiring HBLLS2834 Specification Sheet](#)
- [Specifications - HBLLS2834 Specification Sheet French](#)
- [Specifications - HBLLS2834 Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Temporary Industrial Lighting](#)
- [Video - Temporary Industrial Lighting](#)