



Heavy Duty Products, Switched Twist-Lock®, Industrial Grade, Accessories, Mechanical Interlock, 30A 600V AC, Single Conductor, Terminal Screws, Gray

By Hubbell Wiring Device-Kellems
Catalog # [HBLMITL](#)



Switched Twist-Lock® Industrial Mechanical Interlock 30A 600V, Single Conductor.

Features

- Unfused Mechanical Interlock for Watertight Safety-Shroud
- Virtually Eliminates Possible Circuit Making or Breaking While Under Load
- Compact, Corrosion Resistant Type 4X Non-metallic Enclosure
- Molded Valox Resists Abuse, Corrosion and Enhances Safety
- Unfused mechanical interlock for watertight safety-shroud
- Virtually eliminates possible circuit making or breaking while under load
- Compact, corrosion resistant type 4X non-metallic enclosure
- Molded Valox resists abuse, corrosion and enhances safety

General

Color	<ul style="list-style-type: none"> • Gray • Gris
Item Type	Safety-Shroud Enclosure
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current and voltage • Electrical - Dielectric Voltage - Withstands 3,000V minimum • Electrical - Max. Working Voltage - 600V RMS • Electrical - Operations - Mechanical 10,000 cycles • Electrical 6,000 cycles • Environmental - Flammability - Meets UL 94VO material classification • Environmental - Moisture Resistance - IP66 suitability • Environmental - Operating Temperature - Maximum continuous +75°C Minimum continuous -40°C

Dimensions

Dimensions	11.44 in x 4.88 in x 4.19 in
Height	4.19 in
Length	11.44 in
Weight	3.65 lb
Width	4.88 in

Electrical Ratings

Dielectric Strength	Withstands 3,000V minimum
---------------------	---------------------------

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified TYPE 4, 4X and TYPE 12K Enclosure Rating • Listed to UL Standard
Nema Rating	Type 4X

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Catalog Page - WDK C-3 Catalog Page](#)
[Catalog Page - WDK B-26 Catalog Page](#)
[Catalog Page - WDK B-41 Catalog Page](#)
[Catalog Page - WDK B-20 Catalog Page](#)
[Catalog Page - WDK B-32 Catalog Page](#)
[Catalog Page - WDK B-30 Catalog Page](#)
[Catalog Page - WDK B-34 Catalog Page](#)
[Catalog Page - WDK B-22 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - HBLMITL AutoCAD Drawing](#)
[Installation Manuals - WIRING_HBLMITL_INSTALLINST Literature - Industrial Solutions](#)
[Literature - Circuit-Lock® Motor Disconnects](#)
[Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
[Sales Drawings - WDK_HBLMITL_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

- Environmental - UV Resistance - All exposed materials are UV stabilized
- Mechanical - Impact Resistance - In accordance with UL 746C
- Mechanical - Mounting - External full adjustable feet
- Mechanical - Product Identification - Identification and ratings are part of the external label and receptacle face
- Mechanical - Terminal Identification - In accordance with UL, CSA

Style
Type

For 20A and 30A Devices

- Switched Enclosure
- Switched Enclosure

UPC

783585176802



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBLMITL-SPEC-EN | REV 1/2024