

Locking Devices, Twist-Lock®,
Insul-Lock™ Connectors, 25 Amp,
Power In, Divided, Panel Mount,
Blue

By Hubbell Wiring Device-Kellems
Catalog # [HBLPMIDBL](#)



Locking Devices, Twist-Lock®, Insul-Lock™ Connectors, 25 Amp,
Power In, Divided, Panel Mount, Blue

Features

- Divided Back Plate
- Panel mount devices accept commonly available .25" Sta-Kon™ style connectors
- Industry standard mating

Performance

- Electrical - Amperage - 15A
- Electrical - Voltage - Upto 250V

General

Catalog Number	HBLPMIDBL
EU RoHS Indicator	Contact Manufacturer
Item Type	25 Amp Panel Mount Connectors
Listings	<ul style="list-style-type: none">• cULus• UL Recognized Component rated up to 25A per UL 1977• cUL Recognized Component rated up to 25A per Canadian National Standard C22.2 No. 182.3• Suitable for use in UL 1640 applications
UPC	783585539126

Dimensions

Dimensions	0.94 in x 0.75 in x 1.51 in
Height	1.51 in
Length	0.94 in
Width	0.75 in

Certifications And Compliance

Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalog Page - WDK B-4 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBLPMIDBL AutoCAD Drawing](#)
- [Literature - Insul-Lock™ Connectors and Panel Mounts](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Sales Drawings - WDK_HBLPMIDBL_DRAWING_PDF](#)
- [Specifications - Wiring HBLPMIDBL Specification Sheet](#)
- [Specifications - HBLPMIDBL Specification Sheet French](#)
- [Specifications - HBLPMIDBL Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)