

Heavy Duty Products, IEC Pin and Sleeve, Receptacle, Switched, 60A 250V AC/220-240V AC, 2-Pole 3-Wire Grounding, NEMA 4X/IP69K

By Hubbell Wiring Device-Kellems
Catalog # [HBLS360R6W](#)



Heavy Duty Products, IEC Pin and Sleeve, Receptacle, Switched, 60A 250V AC/220-240V AC, 2-Pole 3-Wire Grounding,NEMA 4X/IP69K

General

Catalog Number	HBLS360R6W
Color	Blue
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	2-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Watertight Receptacle
UPC	783585478548

Electrical Ratings

Amperage Rating	60/63 A
Current / Amperage Rating	60/63 A
Voltage Rating	250 VAC/220-250 VAC
Voltage Rating Description	250 VAC/220-250 VAC

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Logistics

Carton Quantity	6
-----------------	---

Product Assets

- [Catalog Page - WDK G-6 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBLS360R6W AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2660_INSTALLINST](#)
- [Literature - Advantage™ Series Switch-Rated IEC Pin & Sleeve Devices](#)
- [Literature - Safety Product Guide](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Sales Drawings - WDK_HBLS360R_DRAWING_PDF](#)
- [Specifications - Wiring HBLS360R6W Specification Sheet](#)
- [Specifications - HBLS360R6W Specification Sheet French](#)
- [Specifications - HBLS360R6W Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Advantage Series Switch-Rated Pin & Sleeve](#)
- [Video - Advantage Series Switch-Rated Pin & Sleeve](#)