

Heavy Duty Products, IEC Pin and Sleeve, Plug, Switched, 60A 347/600V AC, 4-Pole 5-Wire Grounding, NEMA 4X/IP69K

By Hubbell Wiring Device-Kellems
Catalog # [HBL560P5W](#)



Heavy Duty IEC Pin and Sleeve, Plug, Switched, 60A 347/600V AC, 4-Pole 5-Wire Grounding, NEMA 4X/IP69K.

Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

General

Catalog Number	HBL560P5W
Color	
Number Of Poles	4-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Watertight Plug
UPC	783585479064

Electrical Ratings

Amperage Rating	60 A
Current / Amperage Rating	60 A
Voltage Rating	3 Phase Y 347/600 VAC
Voltage Rating Description	3 Phase Y 347/600 VAC

Conductor Related

Number Of Wires	5-Wire
-----------------	--------

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBL560P5W AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1303_INSTALLINST](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Sales Drawings - WDK_HBL560P5W_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Advantage Series Switch-Rated Pin & Sleeve](#)



A Hubbell brand