

Temporary Lighting Products, LED
Work Light with End Light and Tool
Tap, 25', 16/3 SJTOW Cord

By Hubbell Wiring Device-Kellems
Catalog # [HBLWL25LEDT](#)

Temporary Lighting Products, LED Work Light with End Light
and Tool Tap, 25', 16/3 SJTOW Cord

Features

- Inline Tool Tap with hinged outlet cover to keep dirt and debris out
- Covered on/off switch in handle controls side and end LEDs
- Polycarbonate outer tube is extremely durable

Performance

- Electrical - Lamp Life - 50,000 hours
- Electrical - Light Angle Degree - 130
- Electrical - Light Color - 4700-5200 K
- Electrical - Lumen Output Side/End - 920/120
- Electrical - Rating - 15A 125V
- Electrical - Wattage - 9
- Mechanical - Cord Length - 25 ft.
- Mechanical - Cord Type - 16/3 SJTOW

General

Catalog Number	HBLWL25LEDT
EU RoHS Indicator	Contact Manufacturer
Series	Portable work Light
Specifications	<ul style="list-style-type: none">• Hook Material - Steel• Included - 1 Attached hanging hook• Length - 10.25• Light Type - LED• Outer Tube Material - Polycarbonate• Plug Type - NEMA 5-15P• Width - 1.75



Type	LED Maintenance Worklights
UPC	783585467412

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

Certifications And Compliance

Industry Standard(s)	UL
----------------------	----

Logistics

Carton Quantity	6
-----------------	---

Product Assets

- [Catalog Page - WDK H-16 Catalog Page](#)
- [Catalog Page - WDK H-17 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING_PD2652_INSTALLINST](#)
- [Literature - Safety Product Guide](#)
- [Literature - Temporary Industrial Lighting](#)
- [Literature - Emergency Preparedness for Healthcare](#)
- [Sales Drawings - WDK_HBLWL25LEDT_DRAWING_PDF](#)
- [Specifications - HBLWL25LEDT Specification Sheet French](#)
- [Specifications - Wiring HBLWL25LEDT Specification Sheet](#)
- [Specifications - HBLWL25LEDT Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Temporary Industrial Lighting](#)
- [Video - Temporary Industrial Lighting](#)

