



Temporary Lighting Products, Fluorescent Light, Class 1 Div 1, 12V, 26W, 1800 Lumen Output

By Hubbell Wiring Device-Kellems
Catalog # [HBLXF50120V](#)



Temporary Lighting Products, Fluorescent Light, Class 1 Div 1,
12V, 26W, 1800 Lumen Output.

Features

- Rated for use in Class 1, Div 1, Groups C & D locations & Class 2, Div 1, Groups F & G locations
- No plug included to allow flexibility for user
- Housing is made of corrosion resistant, lightweight, highly durable material.

General

EU RoHS Indicator
Performance

Contact Manufacturer

- Electrical - Lamp Life - 14,000
- Electrical - Light Color - 4100 K
- Electrical - Lumen Output - 1800
- Electrical - Rating - 120V
- Electrical - Wattage - 26
- Environmental - Explosion Proof - Class 1, Div 1 Groups C & D, Class 2, Div 1 Groups F & G
- Mechanical - Cord Length - 50 ft.
- Mechanical - Cord Type - 16/3 SOW

Series
Type

Portable work Light

- Hazardous Location Lights
- Hazardous Location Lights

UPC

783585467313

Certifications and Compliance

Industry Standard(s)

- CSA
- ETL
- UL

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Literature - Food Processing Guide](#)
[Literature - Temporary Industrial Lighting](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Temporary Industrial Lighting](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBLXF50120V-SPEC-EN | REV 1/2024