



Temporary Lighting Products, Incandescent Light, Class 1 Div 1, 12V, 75W, 720 Lumen Output

By Hubbell Wiring Device-Kellems
Catalog # [HBLXI6012V](#)



Temporary Lighting Products, Incandescent Light, Class 1 Div 1,
12V, 75W, 720 Lumen Output.

Features

- Designed for Class 1, Division 1, Groups C & D hazardous locations
- Inline transformer can be placed outside hazardous zone while light is used inside zone and still remain code compliant
- Outer shell is corrosion resistant, non-sparking, and comes with rotating hook
- 360 degree area lighting

General

EU RoHS Indicator
Performance

Contact Manufacturer

- Electrical - Inline Transformer - 12V
- Electrical - Lamp Life - 1,000
- Electrical - Light Angle Degree - 360
- Electrical - Light Color - 2700 K
- Electrical - Lumen Output - 720
- Electrical - Wattage - 75
- Environmental - Explosion Proof - Class 1, Div 1 Groups C & D
- Mechanical - Cord Length - 60 ft.
- Mechanical - Cord Type - 16/3 SOW

Series
Type

Portable work Light

- Hazardous Location Lights
- Hazardous Location Lights

UPC

783585467306

Certifications and Compliance

Industry Standard(s)

- CSA
- ETL
- UL

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Literature - Food Processing Guide](#)
[Literature - Temporary Industrial Lighting](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Temporary Industrial Lighting](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBLXI6012V-SPEC-EN | REV 1/2024