

Kellems Wire Management, Cord Connector, Junior, .08"-.14", 1/4" NPT, Black

By Hubbell Wiring Device-Kellems
Catalog # [HJ1001BPK25](#)



Kellems Wire Management, Cord Connector, Junior, .08"-.14", 1/4" NPT, Black

Features

- Miniature nylon cord connector
- Available in gray or black

Application

Straight Male Connector

Performance

- Environmental - Flammability - Hubbell Juniors have a UL 94V-2 rating
- Environmental - Operating Temperature - -30°F to +225°F (-34°C to +107°C)

General

Catalog Number	HJ1001BPK25
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Juniors® Miniature Cord Connectors
Material	Nylon
Material - Mounting Hardware Series	Locknut or Tapped Opening Miniature
Specifications	• Cord Diameter Range Inches (mm) - .08"-.14" (1.9-3.4) • Material - Nylon • NPT Hub Size - 1/4 Inch • Packaging - Bulk packed 25 per carton
Temperature Rating	Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)

Type	Connector
UPC	783585022871

Dimensions

Display Size	1/4" NPT
Hub Size	1/4"

Conductor Related

Conductor Range	0.08-0.14 in (1.9-3.4 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	IP66

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalog Page - WDK W-76](#)
- [Catalog Page - WDK W-77](#)
- [Catalog Page - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - FOOD & BEVERAGE SOLUTIONS](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - FOOD & BEVERAGE SOLUTIONS](#)
- [Specifications - HJ1001BPK25 Specification Sheet French](#)
- [Specifications - Wiring HJ1001BPK25 Specification Sheet](#)
- [Specifications - HJ1001BPK25 Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Kellems Wire Management Solutions](#)
- [Video - Kellems Wire Management Solutions](#)