



Wiring Device-Kellems

Straight Blade Receptacles, Decorator Duplex, Commercial, Corrosion Resistant, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Back and Side Wired, White

By Hubbell Wiring Device-Kellems
Catalog # IG15DRW



Straight Blade Receptacle, Decorator Duplex, Commercial Grade, Corrosion Resistant, 15A 125V, 2- Pole 3-Wire Grounding, 5-15R, Back and Side Wired.

Features

- Triangle marking on face indicates isolated ground
- Aesthetic Style Line® decorator design
- Triple wipe contacts

Application

Heavy Duty

General

Color	<ul style="list-style-type: none"> • White • Blanc
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Isolated Ground
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
UPC	783585146867

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	1875

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Engineering Drawing - IG15DRW AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1579_PD2305_INSTALLINST](#)
[Sales Drawings - WDK_IG15DRW_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK_CA-IG15DRW-SPEC-EN | REV 6/2023