

Straight Blade Devices, Receptacles,
Decorator Duplex, Commercial Grade,
Corrosion Resistant, Smooth Face, 20A
125V, 2- Pole 3-Wire Grounding, 5-20R.

By Hubbell Wiring Device-Kellems
Catalog # [IG20DR](#)

Straight Blade Devices, Receptacles, Decorator Duplex,
Commercial Grade, Corrosion Resistant, Smooth Face, 20A 125V,
2- Pole 3-Wire Grounding, 5-20R, Back and Side Wired, Orange.

Features

- Triangle marking on face indicates isolated ground
- Aesthetic Style Line® decorator design
- Triple wipe contacts

Application

Commercial Grade

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 V-2, Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact), Mechanical - Product Identification - Ratings are a permanent part of the device, Mechanical - Terminal Accommodation - #12-#10 AWG copper stranded or solid conductor only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-20R
Industry Standard(s)	• Certified to CSA C22.2, No. 42 • Fed. Spec. WC596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186

Conductor

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	20 A
Voltage Rating Description	125 V
Dielectric Strength	Withstands 2,000V minimum



Current Rating	20 A
Voltage Rating	125 V
Wattage	2500 W
Connectivity	Back and Side Wired
Phase	Single Phase
Current / Amperage Rating	20 A

Dimensions

Length	1.29 in
Display Size	Standard Sized Product
Weight	0.15 lb.
Height	3.28 in
Width	1.06 in
Dimensions	1.29 in x 1.06 in x 3.28 in

General

Color	Orange
Style	Style Line Decorator
Series	Commercial Specification Grade

Specifications	• Automatic Self-grounding Staple - Stainless steel • Base - Nylon • Face - Nylon • Ground Contacts - Brass • Mounting Screws - Galvanized Steel • Mounting Strap - .040 in. (1) Galvanized steel • Power Contacts - .030 in. (.8) Brass • Terminal Screws - Plated steel • Wire Clamp - .062 in. (1.6) Nickel plated steel
UPC	783585147864
Type	Standard Duplex
Material - Mounting Hardware	Screw Mounting
Item Type	Decorator Duplex
Material	Nylon

Logistics

Pallet Quantity	9000
-----------------	------

Carton Quantity	10	Product Assets
Operational		Catalog [English]
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact	Catalog Page [English]
Horsepower - Maximum	1	Catalog Page [English]
		Installation Manual [Spanish, French, English]
 A Hubbell brand		© 2026 Hubbell Incorporated. All rights reserved WDK_CA-IG20DR-SPEC-EN REV 5/2026