

Straight Blade Devices,  
Receptacles, Decorator Duplex,  
Commercial Grade, Corrosion  
Resistant, Smooth Face, 20A 125V,  
2- Pole 3-Wire Grounding, 5-20R.

By Hubbell Wiring Device-Kellems  
Catalog # [IG20DRWHI](#)

Straight Blade Devices, Receptacles, Decorator Duplex,  
Commercial Grade, Corrosion Resistant, Smooth Face, 20A 125V,  
2- Pole 3-Wire Grounding, 5-20R, Back and Side Wired, White.

Features

- Triangle marking on face indicates isolated ground
- Aesthetic Style Line® decorator design
- Triple wipe contacts

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	IG20DRWHI
Color	White
EU RoHS Indicator	Yes
Horsepower - Maximum	1
Item Type	Decorator Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Commercial Specification Grade
Specifications	<ul style="list-style-type: none"><li>• Automatic Self-grounding Staple - Stainless steel</li><li>• Base - Nylon</li><li>• Face - Nylon</li><li>• Ground Contacts - Brass</li></ul>



Style	• Mounting Screws - Galvanized Steel
UPC	• Mounting Strap - .040 in. (1) Galvanized steel
	• Power Contacts - .030 in. (.8) Brass
	• Terminal Screws - Plated steel
	• Wire Clamp - .062 in. (1.6) Nickel plated steel
	Style Line Decorator
	783585147871

Dimensions

Dimensions	1.29 in x 1.06 in x 3.28 in
Display Size	Standard Sized Product
Height	3.28 in
Length	1.29 in
Weight	0.15 lb
Width	1.06 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA C22.2, No. 42</li><li>• Fed. Spec. WC596</li><li>• NEMA® WD-6 Compliant</li><li>• UL Listed to UL498 File No. E2186</li></ul>
Nema Rating	5-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK M-18 Catalog Page](#)
- [Catalog Page - WDK A-30 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - IG20DRWHI AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD1579\\_PD2305\\_INSTALLINST](#)
- [Sales Drawings - WDK\\_IG20DRWHI\\_DRAWING\\_PDF](#)
- [Specifications - IG20DRWHI Specification Sheet French](#)
- [Specifications - Wiring IG20DRWHI Specification Sheet](#)
- [Specifications - IG20DRWHI Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand