

EdgeConnect™ Twist-Lock®
Locking Devices, Single Receptacle,
15A 125V, 2-Pole 3-Wire Grounding

By Hubbell Wiring Device-Kellems
Catalog # [IG4710ST](#)

Locking Devices, EdgeConnect™ Twist-Lock®, Isolated Ground
Industrial, Single Receptacle, 15A 125V, 2-Pole 3-Wire Grounding,
L5-15R, Screw Terminal, Orange

Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.

Application

Industrial

General

Catalog Number	IG4710ST
Environmental Conditions	IP20 Suitability
Material	Nylon
Mounting Type	Screw Mount
Number Of Poles	2
Series	EdgeConnect™
Size	Standard Sized Product
Style	Locking Devices
Temperature Rating	Maximum Continuous 75°C, Minimum -40°C (w/o impact)
Type	Receptacle
UPC	783585719672

Electrical Ratings

Current / Amperage Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC



Conductor Related

Number Of Wires	3
-----------------	---

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Listed to UL 498• Fed.Spec. W-C-596• Certified to CSA C22.2 No.42
Nema Rating	L5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Brochures - EdgeConnect Brochure French](#)
- [Brochures - EdgeConnect Brochure](#)
- [Catalog Page - WDK B-13 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - M14595_ACAD](#)
- [Installation Manuals - PD3024](#)
- [Literature - EdgeConnect™ Technology FAQ](#)
- [Literature - EdgeConnect™ Technology](#)
- [Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
- [Sales Drawings - M14595](#)
- [Specifications - IG4710ST Specification Sheet](#)
- [Specifications - Wiring IG4710ST specification sheet](#)
- [Specifications - IG4710ST Specification Sheet French](#)
- [Warranty - Industrial & Commercial Products](#)