



Straight Blade Devices, Receptacles, Duplex, Commercial Grade, Isolated Ground, 2-Pole 3- Wire Grounding, 15A 125V, 5-15R, Orange, Single Pack.

By Hubbell Wiring Device-Kellems
Catalog # [IG5252](#)



Straight Blade Hubbell-PRO™ Heavy Duty Isolated Ground
Duplex Receptacle 15A, 2-Pole, 3-Wire Grounding, 125V, 5-15R,
Orange.

Features

- Triangle marking on face indicates isolated ground
- Slender/compact design
- Smooth Face

Application

Hubbell-Pro Heavy Duty Specification Grade

General

Color	<ul style="list-style-type: none"> • Orange • Orange
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 V-2 • Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or

Dimensions

Dimensions	3.28 in x 1.57 in x 1.07 in
Display Size	Standard Sized Product
Height	1.07 in
Length	3.28 in
Weight	0.15 lb
Width	1.57 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA 22.2, No. 42 File 285 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
----------------------	---

Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK M-18 Catalog Page](#)

solid conductor only

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

[Catalog Page - WDK A-27 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - IG5252 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1579_PD2305_INSTALLINST](#)
[Sales Drawings - WDK_IG5252_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

Series

Hubbell-PRO

Style

Smooth Face

Type

- Isolated Ground
- Isolated Ground

UPC

783585146706



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-IG5252-SPEC-EN | REV 1/2024