

Straight Blade Devices, Tamper Resistant
Duplex Receptacle, Isolated Ground,
Commercial Grade, 20A 125V, 5-20R

By Hubbell Wiring Device-Kellems
Catalog # [IG5352TR](#)

Straight Blade Devices, Tamper Resistant Duplex Receptacle,
Isolated Ground, Commercial Grade, 20A 125V, 2-Pole 3-Wire
Grounding, 5-20R, Back and Side Wired, Orange, Single Pack

Features

- Triangle marking on face indicates isolated ground
- Tamper-Resistant
- Smooth Face
- Wrap-around galvanized steel strap

Application

Hubbell-Pro Heavy Duty Specification Grade

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 V-2, Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact), Mechanical - Product Identification - Ratings are a permanent part of the device, Mechanical - Terminal Accommodation - #12-#10 AWG copper stranded or solid conductor only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	5-20R
Industry Standard(s)	• Certified to CSA 22.2, No. 42 File 285 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186

Conductor

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	20 A
Voltage Rating Description	125 V
Dielectric Strength	Withstands 2,000V minimum
Current Rating	20 A



Voltage Rating	125 V
Wattage	2500 W
Connectivity	Back and Side Wired Screw Terminals
Phase	Single Phase
Current / Amperage Rating	20 A

Dimensions

Length	3.28 in
Display Size	Standard Sized Product
Weight	0.25 lb.
Height	1.07 in
Width	1.57 in
Dimensions	3.28 in x 1.57 in x 1.07 in

General

Color	Brown
Style	Smooth Face
Series	Hubbell-PRO
Specifications	• Automatic Self-grounding Clip - Stainless steel • Base - Nylon • Clamp - Nickel plated steel • Face - Nylon • Ground Contacts - .031" (.8) Brass • Mounting Screws - Stainless Steel • Mounting Strap - Galvanized steel • Power Contacts - .031 in. (.8) Brass • Terminal Screws - Brass
UPC	783585540047
Type	Isolated Ground
Material - Mounting Hardware	Screw Mounting
Item Type	Traditional Duplex
Material	Nylon

Logistics

Pallet Quantity	8000
Carton Quantity	10

Operational

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact °C
Horsepower - Maximum	1

Product Assets
[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)



A Hubbell brand