



# Hospital Grade Surge Suppression Receptacle, Isolated Ground, 15A 125V, 5-15R, Ivory

By Hubbell Wiring Device-Kellems  
Catalog # IG8262ISA

Hospital Grade Surge Suppression Receptacle, Isolated Ground, 15A 125V, 5-15R, Ivory.



## Features

- High-impact nylon face resists breakage
- Automatic grounding clip attached to bridge
- Power-on indicator light verifies instantly that power is available
- Distinctive surge symbol for visual identification of surge suppression receptacle

## Application

Decorator Duplex with Light and Alarm

## General

Color	Ivory
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Performance	<ul style="list-style-type: none"> <li>• Electrical - Frequency - 60Hz</li> <li>• Electrical - Protection Modes - Normal and Common Modes</li> <li>• Electrical - Response Time - Approximately 5 ns</li> <li>• Electrical - Transient Suppression - Peak Energy (10 X 100 <math>\mu</math>s) Peak Current (8 X 20 <math>\mu</math>s)</li> <li>• Electrical - Voltage - 120V AC + 10% - 15%</li> <li>• Environmental - Flammability - UL 94V-2</li> <li>• Environmental - Operating Temperature - 32°F to 140°F (0°C to 60°C)</li> </ul>
Response Time	5
Series	Hospital Grade
Style	Isolated Ground
Type	Duplex

## Dimensions

Display Size Standard

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified to Specification C22.2 No. 42</li> <li>• Listed to UL Standards 498 Receptacles</li> <li>• UL Listed File E2186</li> </ul>
Nema Rating	5-15R

## Logistics

Carton Quantity 10

## Product Assets

- [Catalog Page - WDK L-16 Catalog Page](#)
- [Catalog Page - WDK M-13 Catalog Page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Catalogs - Wiring Device-Kellems Full Catalog](#)
- [Engineering Drawing - IG8262ISA AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD1152\\_INSTALLINST](#)
- [Literature - Duct Products Guide](#)
- [Literature - SpikeShield® Power Quality Surge Protective Devices](#)
- [Sales Drawings - WDK\\_IG8262\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)



**A proud member of the Hubbell Family.**