



Hospital Grade Surge Suppression Receptacle, 20A 125V, 5-20R, Grange

By Hubbell Wiring Device-Kellems
Catalog # IG8362RSA



Hospital Grade Surge Suppression Receptacle, 20A 125V, 5-20R, Grange.

Features

- High-impact nylon face resists breakage
- Automatic grounding clip attached to bridge
- Power-on indicator light verifies instantly that power is available
- Distinctive surge symbol provides quick visual identification of surge suppression receptacle

Application

Decorator Duplex with Light and Alarm

General

Color	Red
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Performance	<ul style="list-style-type: none"> • Electrical - Frequency - 60Hz • Electrical - Protection Modes - Normal and Common Modes • Electrical - Response Time - Approximately 5 ns • Electrical - Transient Suppression - Peak Energy (10 X 100 μs) Peak Current (8 X 20 μs) • Electrical - Voltage - 120V AC + 10% - 15% • Environmental - Flammability - UL 94V-2 • Environmental - Operating Temperature - 32°F to 140°F (0°C to 60°C)
Response Time	5
Series	Hospital Grade
Style	Isolated Ground

Dimensions

Display Size Standard

Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Certifications and Compliance

- | | |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none"> • CSA Certified to Specification C22.2 No. 42 • Listed to UL Standards 498 Receptacles • UL Listed File E2186 |
|----------------------|---|

Nema Rating 5-20R

Logistics

Carton Quantity 10

Product Assets

- [Catalog Page - WDK L-16 Catalog Page](#)
- [Catalog Page - WDK M-13 Catalog Page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Catalogs - Wiring Device-Kellems Full Catalog](#)
- [Engineering Drawing - IG8362RSA AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1152_INSTALLINST](#)
- [Literature - Duct Products Guide](#)
- [Literature - Healthcare Application Guide](#)
- [Literature - SpikeShield® Power Quality Surge Protective Devices](#)
- [Sales Drawings - WDK_IG8362_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)

Type
UPC

Duplex
783585060958



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK_CA-IG8362RSA-SPEC-EN | REV 6/2023