

Heavy Duty Products, Insulgrip Pin and Sleeve Devices, Industrial Grade, Female, Replacement Interior, For 100A 3-Wire Style 1

By Hubbell Wiring Device-Kellems  
Catalog # [IN3100FS1](#)

Heavy Duty Products, Insulgrip Pin and Sleeve Devices, Industrial Grade, Female, Replacement Interior, For 100A 3-Wire Style 1, Furnished with Screws, Black Thermoset Polyester

Features

- Thermoset polyester contact carrier
- Pin Chamber confines arcing within the interior
- Large, funneled terminal entrance holes

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 3,000V AC, Electrical - Max Working Voltage - 600V AC RMS, Environmental - Flammability - UL94-5VA and V-O classification, Environmental - Ingress Protection - IP67 Suitability, Environmental - Operating Temperatures - Maximum Continuous: 75° C, Minimum -40° C w/o impact, Mechanical - Impact Resistance - In accordance with UL746C, Mechanical - Product Identification - Identification and ratings are a part of the external label and molded into the receptacle mount, Mechanical - Terminal Identification - Terminals identified in accordance with North American and International conventions

Specifications

|                          |                           |
|--------------------------|---------------------------|
| Nema Rating              | Non-NEMA                  |
| Industry Standard(s)     | UL Listed                 |
| Environmental Conditions | Watertight When Installed |
| EU RoHS Indicator        | Yes                       |

Conductor

|                 |        |
|-----------------|--------|
| Number Of Poles | 2-Pole |
| Number Of Wires | 3-Wire |

Current

|                 |                  |
|-----------------|------------------|
| Amperage Rating | 100 A            |
| Voltage Rating  | 600/250V AC/DC V |



|                            |                          |
|----------------------------|--------------------------|
| Voltage Rating Description | 600/250V AC/DC           |
| Connectivity               | Pressure Terminal Screws |
| Current / Amperage Rating  | 100 A                    |

Dimensions

|              |                        |
|--------------|------------------------|
| Display Size | Standard Sized Product |
|--------------|------------------------|

General

|                              |                                                                                                                                                                                                                                               |
|------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Specifications               | <ul style="list-style-type: none"><li>• Assembly Screws - Stainless Steel</li><li>• Contact Carrier - Thermoset Polyester</li><li>• Gaskets - Neoprene</li><li>• Ground/Phase Pins - Brass</li><li>• Hinge Spring - Stainless Steel</li></ul> |
| Style                        | For Receptacles/Connectors, Style 1                                                                                                                                                                                                           |
| UPC                          | 783585323961                                                                                                                                                                                                                                  |
| Type                         | Replacment Interior                                                                                                                                                                                                                           |
| Material - Mounting Hardware | Screw Mounting                                                                                                                                                                                                                                |
| Item Type                    | Replacement Interior                                                                                                                                                                                                                          |
| Material                     | Thermoplastic                                                                                                                                                                                                                                 |
| Series                       | Accessories                                                                                                                                                                                                                                   |

Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 5 |
|-----------------|---|

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)