

Heavy Duty Products, Insulgrip Pin and Sleeve Devices, Industrial Grade, Female, Replacement Interior, For 100A 4-Wire Style 2

By Hubbell Wiring Device-Kellems
Catalog # [IN4100FS2](#)

Heavy Duty Products, Insulgrip Pin and Sleeve Devices, Industrial Grade, Female, Replacement Interior, For 100A 4-Wire Style 2, Furnished with Screws, Black Thermoset Polyester

Features

- Thermoset polyester contact carrier
- Pin Chamber confines arcing within the interior
- Large, funneled terminal entrance holes

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 3,000V AC, Electrical - Max Working Voltage - 600V AC RMS, Environmental - Flammability - UL94-5VA and V-O classification, Environmental - Ingress Protection - IP67 Suitability, Environmental - Operating Temperatures - Maximum Continuous: 75° C, Minimum -40° C w/o impact, Mechanical - Impact Resistance - In accordance with UL746C, Mechanical - Product Identification - Identification and ratings are a part of the external label and molded into the receptacle mount, Mechanical - Terminal Identification - Terminals identified in accordance with North American and International conventions

Specifications

Environmental Conditions	Watertight When Installed
EU RoHS Indicator	Yes
Nema Rating	Non-NEMA
Industry Standard(s)	UL Listed

Conductor

Number Of Wires	4-Wire
Number Of Poles	3-Pole

Current

Amperage Rating	100 A
Voltage Rating Description	600/250V AC/DC



Voltage Rating	600/250V AC/DC V
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	100 A

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

Style	For Receptacles/Connectors, Style 2
Series	Accessories
Specifications	• Assembly Screws - Stainless Steel • Contact Carrier - Thermoset Polyester • Gaskets - Neoprene • Ground/Phase Pins - Brass • Hinge Spring - Stainless Steel
UPC	783585324197
Type	Replacment Interior
Material - Mounting Hardware	Screw Mounting
Item Type	Replacement Interior
Material	Thermoplastic

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)