

Lighting Controls Residential / Light Commercial Slide Dimmer Switch, 0-10V LED - Single Pole, Three Way, 10A 120VAC, 5A 277VAC, White

By Hubbell Wiring Device-Kellems
Catalog # [LCD0108SW](#)



Take control of the lighting ambiance in your home while reducing your energy footprint by combining our Low Voltage Slide Dimmer Switch with efficient LED light lamps. Designed to work with a range of ballasted LED lamps for Residential and Light Commercial usage. Customize the feel and comfort of your lighting with Hubbell's Residential Dimmers.

Features

- Control for 0-10V LED loads only
- Trim Adjustment for Fine Tuning
- Digital Circuit Controlled
- Decorator Slide Styling
- UL/cUL listed

General

Catalog Number	LCD0108SW
Lamp Type	0-10 V LED Lamps with or without Ballast
Number Of Poles	1, 3, 4
UPC	783585565804

Dimensions

Depth	2.0 in. in
Height	2 in
Width	2 in

Electrical Ratings

Current / Amperage Rating	0-10 V / 10 A
Frequency Rating	60 Hz
Output Voltage	0-10 V
Voltage Rating	120 V

Logistics

Carton Quantity 10

Product Assets

[Brochures - WDK Dimmers Brochure CA](#)
[Brochures - WDK Dimmers Brochure CA French](#)
[Catalog Page - WDK Z-19 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Literature - Residential Catalog](#)
[Literature - Wall Dimmers and Lighting Controls](#)
[Sales Drawings - M14555](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_CA-LCD0108SW-SPEC-EN | REV 6/2024