

# Lighting Controls Residential Rocker Dimmer Switch, 200W LED/CFL, 600W Incandescent 1.5A - Single Pole, Three Way, 120VAC, Light Almond

By Hubbell Wiring Device-Kellems  
Catalog # [LCD150DLA](#)



Take control of the lighting ambiance in your home while reducing your energy footprint by combining our Rocker Dimmer Switch with efficient LED light bulbs. Designed to work with a full range of LED/CFL and even traditional Incandescent bulbs using digital trim adjust to reduce flicker and offer the best range of light use. Customize the feel and comfort of your home's lighting with Hubbell's Residential Dimmers.

## Features

- Trim Adjustment for Fine Tuning
- Digital Circuit Controlled
- Decorator Rocker Styling
- UL/cUL listed

## General

Catalog Number	LCD150DLA
Lamp Type	Most Bulbs, Dimmable
Number Of Poles	1, 3, 4
UPC	783585565729

## Dimensions

Depth	2.0 in. in
Height	2 in
Width	2 in

## Electrical Ratings

Current / Amperage Rating	200W / 1.5 A
Frequency Rating	60 Hz
Output Voltage	120 VAC
Voltage Rating	120 VAC

## Logistics

Carton Quantity 10

## Product Assets

[Brochures - WDK Dimmers Brochure CA](#)  
[Brochures - WDK Dimmers Brochure CA French](#)  
[Catalog Page - WDK Z-19 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Residential Catalog](#)  
[Literature - Wall Dimmers and Lighting Controls](#)  
[Sales Drawings - M14552](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_CA-LCD150DLA-SPEC-EN | REV 6/2024