

Lighting Controls Residential Rocker Dimmer Switch, 300W LED/CFL, 600W Incandescent 2.5A - Single Pole, Three Way, 120VAC, White

By Hubbell Wiring Device-Kellems
Catalog # [LCD300DW](#)



Take control of the lighting ambiance in your home while reducing your energy footprint by combining our Rocker Dimmer Switch with efficient LED light bulbs. Designed to work with a full range of LED/CFL and even traditional Incandescent bulbs using digital trim adjust to reduce flicker and offer the best range of light use. Enjoy added convenience with in-use Indicator light. Customize the feel and comfort of your home's lighting with Hubbell's Residential Dimmers.

General

Lamp Type	Most Bulbs, Dimmable
Number Of Poles	1, 3, 4
UPC	783585565866

Dimensions

Depth	2.0 in. in
Height	2 in
Width	2 in

Electrical Ratings

Current / Amperage Rating	300W / 2.5 A
Frequency Rating	60 Hz
Output Voltage	120 VAC
Voltage Rating	120 VAC

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Brochures - WDK Dimmers Brochure CA](#)
[Brochures - WDK Dimmers Brochure CA French](#)
[Catalog Page - WDK Z-19 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Literature - Residential Catalog](#)
[Literature - Wall Dimmers and Lighting Controls](#)
[Sales Drawings - M14430](#)

