

Kellems Wire Management, Cord
Connectors, 90 Degree Male
.75-.88", 3/4", Nylon

By Hubbell Wiring Device-Kellems
Catalog # [NHC1038CR](#)

Kellems Wire Management, Cord Connectors, 90 Degree Male
.75-.88", 3/4", Nylon

Features

- Nylon cord connector resists corrosion
- Connector body is a one-piece design with machined threads
- Tapered interior seats the bushing evenly for a liquidtight seal

Application

90 Degree Male- Form 3

Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC.
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

General

Catalog Number	NHC1038CR
Color Code	Orchid
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Nylon
Material - Mounting Hardware Series	Locknut or Tapped Opening Standard Duty
Specifications	<ul style="list-style-type: none">• Cord Diameter Inches (mm) - .75"- .88" (19.0-22.2)• Form Size - F3• Material - Gray Nylon• NPT Hub Size - 3/4 Inch
Temperature Rating	Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)
Type	90° Male



UPC 783585208800

Dimensions

Display Size 3/4" NPT
Hub Size 3/4"

Conductor Related

Conductor Range 0.75- 0.88 in (19.0- 22.2 mm)
Number of Conductors Single

Certifications And Compliance

Industry Standard(s) UL Listed
Nema Rating NEMA Type 4, 4X, 12 and 13
Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 15

Product Assets

[Catalog Page - WDK W-72 Catalog Page](#)
[Catalog Page - WDK W-71 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD1856_INSTALLINST](#)
[Literature - Wire Management Solutions Brochure](#)
[Literature - FOOD & BEVERAGE SOLUTIONS](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - FOOD & BEVERAGE SOLUTIONS](#)
[Specifications - NHC1038CR Specification Sheet French](#)
[Specifications - Wiring NHC1038CR Specification Sheet](#)
[Specifications - NHC1038CR Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Kellems Wire Management Solutions](#)
[Video - Kellems Wire Management Solutions](#)