

Wallplates and Box Covers,
Wallplate, Nylon, 1-Gang, 1) Toggle,
Ivory

By Hubbell Wiring Device-Kellems
Catalog # [NP1I](#)



Wallplates and Box Covers, Wallplate, Nylon, 1-Gang, 1) Toggle,
Ivory

Features

- Reinforcement ribs for extra strength
- Captive screw feature holds mounting screw in place
- High-impact, self-extinguishing nylon material
- Smooth, easy to clean finish

Application

Protection against contact of live terminals and wiring. Provides finished look to installation.

General

Catalog Number	NP1I
Color	Ivory
Construction	Molded
Cutout	1) Toggle
EU RoHS Indicator	Yes
Item Type	Toggle Switch Plate
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number of Gang(s)	1-Gang
Operating Temperature	-40°Cto 85 °C
Orientation	Vertical Mount
Size	Standard
Specifications	<ul style="list-style-type: none">• Appearance - Smooth• Mounting Screws - Steel painted, slotted head• Plate Material - Nylon• Plate Openings - Toggle switch• Plate Type - 1-Gang
Style	1-Toggle

Type	Toggle
UPC	883778101601

Dimensions

Dimensions	4.62 in x 2.87 in x 0.25 in
Display Size	Standard Sized
Height	0.25 in
Length	4.62 in
Thickness	0.25
Weight	0.25 lb
Width	2.87 in

Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - NP1I AutoCAD Drawing](#)
[Literature - Residential Product Guide](#)
[Literature - Hubbell Marine Full Line Catalog](#)
[Sales Drawings - WDK_NP1_DRAWING_PDF](#)
[Specifications - NP1I Specification Sheet](#)
[Specifications - Wiring NP1I Specification Sheet](#)
[Specifications - NP1I Specification Sheet French](#)
[Warranty - tradeSELECT™ and netSELECT®](#)

