

Signal and Control Products,
Industrial Ethernet, NEMA 4X
Enclosure, Cat5e, 15A 125V
Receptacle, with 3A Circuit Breaker

By Hubbell Wiring Device-Kellems
Catalog # [P4X155EB](#)

Signal and Control Products, Industrial Ethernet, NEMA 4X
Enclosure, Cat5e, 15A 125V Receptacle, with 3A Circuit Breaker

Features

- Protective clear cover
- Overcurrent protection
- Finger-safe contacts
- Stainless steel snap latch

Application

15A 125V Power, Cat 5e Ethernet Access and 3A Circuit Breaker

Performance

- Electrical - Circuit Breaker - 3A
- Electrical - Data Jack - Cat. 5e
- Electrical - GFCI - Conforms to UL 943 2006 requirement
- Electrical - In-Cabinet Receptacle - GFCI protected
- Environmental - Enclosure - NEMA Type 4, 12 and NEMA Type 4X

General

Catalog Number	P4X155EB
Color	Gray, Clear
EU RoHS Indicator	Yes
Enclosure Type	NEMA 4X
Item Type	Industrial Connectivity
Material	Composite
Material - Mounting Hardware	Screw Mounting
Specifications	• Cover - Clear Polycarbonate (UV Rated) • Finish - Powder Coat • Housing - Cast Aluminum



UPC
783585524788

- Latch - Stainless steel

Dimensions

Height 5.5 in
Width 2.3 in

Conductor Related

Cable Entry Plug-In

Certifications And Compliance

Industry Standard(s)

- CSA Certified
- UL Recognized

Logistics

Carton Quantity 20

Product Assets

[Catalog Page - WDK I-15 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - P4X155EB AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2170_INSTALLINST](#)
[Literature - Food Processing Guide](#)
[Sales Drawings - WDK_P4X155EB_DRAWING_PDF](#)
[Specifications - P4X155EB Specification Sheet French](#)
[Specifications - P4X155EB Specification Sheet](#)
[Specifications - Wiring P4X155EB specification sheet](#)
[Warranty - Industrial & Commercial Products](#)