

# Signal And Control, Linkosity, Cordset, Female, Double End, 90 Degree, 3-Wire, 10A 600V AC, PA Wire Code, 10' Length, Stainless Hex Nuts

By Hubbell Wiring Device-Kellems  
Catalog # [PG1003PA010S](#)

Signal And Control, Linkosity, Cordset, Female, Double End, 90 Degree, 3-Wire, 10A 600V AC, PA Wire Code, 10' Length, Stainless Hex Nuts.

## General

Application	Quick Connect/Disconnect Signal and Control
Catalog Number	PG1003PA010S
Color	
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Single Ended Cable, 90 Degree Female Connector
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585184869

## Dimensions

Outside Diameter	0.71
------------------	------

## Electrical Ratings

Amperage Rating	10 A
Current / Amperage Rating	10 A
Current Rating	10 A
Voltage Rating	600V kV

## Conductor Related

Conductor Size	#12 AWG
Conductor Type	Copper
Number of Conductors	3-Pole
Strands	Multi



## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING\\_PD2038\\_INSTALLINST](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_CA-PG1003PA010S-SPEC-EN | REV 6/2024