

Signal And Control, Linkosity, Cordset, Female, Double End, 90 Degree, 10-Wire, 10A 600V AC, PE Wire Code, 20' Length

By Hubbell Wiring Device-Kellems
Catalog # [PG1010PE020](#)

Signal And Control, Linkosity, Cordset, Female, Double End, 90 Degree, 10-Wire, 10A 600V AC, PE Wire Code, 20' Length.



General

Application	Plug Together Power Distribution, No Pass Thru
Catalog Number	PG1010PE020
Color	
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Conduit Feed Pre-Wired Box
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	10-Pole
UPC	783585185064

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	5 A
Connectivity	Plug Together
Current / Amperage Rating	5 A
Current Rating	5 A
Phase	Single Phase Control
Voltage Rating	250V AC Max kV
Wattage	1250

Conductor Related

Number Of Wires	11-Wire Grounding
Wire Size	#12 AWG

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING_PD2038_INSTALLINST](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_CA-PG1010PE020-SPEC-EN | REV 6/2024