

Linkosity, Double Ended Cable, 20A  
Single, 3W, 50'

By Hubbell Wiring Device-Kellems  
Catalog # [PH2303PB050](#)

Linkosity, Double Ended Cable, 20A Single, 3W, 50'

Features

- Linkosity
- Double Ended Cable
- 20A Single
- 3W
- 50'

Application

Quick Connect/Disconnect Signal and Control

General

Catalog Number	PH2303PB050
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Double Ended Cable, Male/Female Straight Connectors
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585116235

Dimensions

Outside Diameter	0.71
------------------	------

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	600V kV

Conductor Related

Conductor Size	#12 AWG, #10 AWG Neutral
Conductor Type	Copper
Number of Conductors	3-Pole
Strands	Multi

Logistics

Carton Quantity	2
-----------------	---

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - PH2303PB050 AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD1996\\_INSTALLINST](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Sales Drawings - WDK\\_PH2303\\_DRAWING\\_PDF](#)
- [Specifications - PH2303PB050 Specification Sheet French](#)
- [Specifications - WIRING\\_PH2303PB050\\_spec](#)
- [Specifications - PH2303PB050 Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Linkosity®](#)

