

Linkosity, Male Female Extension
Cable, 20A Single, 4P, 25'

By Hubbell Wiring Device-Kellems
Catalog # [PH2304PB025](#)

Linkosity, Male Female Extension Cable, 20A Single, 4P, 25'

Features

- Linkosity
- Male Female Extension Cable
- 20A Single
- 4P
- 25'

Application

Quick Connect/Disconnect Signal and Control

General

Catalog Number	PH2304PB025
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Double Ended Cable, Male/Female Straight Connectors
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585355108

Dimensions

Outside Diameter	0.75
------------------	------

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	600V kV

Conductor Related

Conductor Size	#12 AWG, #10 AWG Neutral
Conductor Type	Copper
Number of Conductors	4-Pole
Strands	Multi

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - PH2304PB025 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1996_INSTALLINST](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Sales Drawings - WDK_PH2304_DRAWING_PDF](#)
- [Specifications - PH2304PB025 Specification Sheet](#)
- [Specifications - PH2304PB025 Specification Sheet French](#)
- [Specifications - Wiring PH2304PB025 specification sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Linkosity®](#)

