

Signal and Control Products,
Industrial Ethernet, NEMA 12/4
Enclosure, 15A 125V, GFCI
Receptacle

By Hubbell Wiring Device-Kellems
Catalog # [PR20](#)

Signal and Control Products, Industrial Ethernet, NEMA 12/4
Enclosure, 15A 125V, GFCI Receptacle

Features

- Protective clear cover
- Finger-safe contacts
- Stainless steel snap latch

Performance

- Electrical - GFCI - Conforms to UL 943 2006 requirement
- Electrical - In-Cabinet Receptacle - GFCI protected
- Environmental - Enclosure - NEMA Type 4 and 12

General

Catalog Number	PR20
EU RoHS Indicator	Yes
Enclosure Type	NEMA 12/4
Item Type	Industrial Connectivity
Material	Composite
Material - Mounting Hardware	Screw Mounting
Specifications	<ul style="list-style-type: none">• Cover - Clear Polycarbonate (UV Rated)• Finish - Powder Coat• Housing - Cast Aluminum• Latch - Stainless steel
UPC	783585524825

Dimensions

Cubic Capacity	100.878 cu.in
Depth	4.6
Height	5.1 in
Width	4.3 in



Electrical Ratings

Current / Amperage Rating	15 A
---------------------------	------

Conductor Related

Cable Entry	Plug-In
-------------	---------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified• UL Recognized
----------------------	---

Logistics

Carton Quantity	25
Pallet Quantity	450

Product Assets

- [BIM - PR4](#)
- [BIM - PR3](#)
- [BIM - PR2](#)
- [Catalog Page - WDK I-15 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - PR20 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2170_INSTALLINST](#)
- [Literature - Safety Product Guide](#)
- [Literature - Food Processing Guide](#)
- [Literature - Industrial Solutions](#)
- [Sales Drawings - WDK_PR20_DRAWING_PDF](#)
- [Specifications - PR20 Specification Sheet French](#)
- [Specifications - Wiring PR20 specification sheet](#)
- [Specifications - PR20 Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)