

Signal and Control Products,
Industrial Ethernet, NEMA 12/4
Enclosure, Cat 5e, 15A 125V, GFCI
Receptacle

By Hubbell Wiring Device-Kellems
Catalog # [PR205E](#)

Signal and Control Products, Industrial Ethernet, NEMA 12/4
Enclosure, Cat 5e, 15A 125V, GFCI Receptacle

Features

- Protective clear cover
- Overcurrent protection
- Finger-safe contacts
- Stainless steel snap latch

Performance

- Electrical - Circuit Breaker - 3A
- Electrical - Data Jack - Cat. 5e
- Electrical - GFCI - Conforms to UL 943 2006 requirement
- Electrical - In-Cabinet Receptacle - GFCI protected
- Environmental - Enclosure - NEMA Type 4, 12 and NEMA Type 4X

General

Catalog Number	PR205E
Color	Gray
EU RoHS Indicator	Yes
Enclosure Type	NEMA 12/4
Item Type	Industrial Connectivity
Material	Composite
Material - Mounting Hardware	Screw Mounting
Specifications	• Cover - Clear Polycarbonate (UV Rated) • Finish - Powder Coat • Housing - Cast Aluminum • Latch - Stainless steel
UPC	783585524757

Dimensions

Cubic Capacity	78.336 cu.in
Depth	3.2



Height	5.1 in
Width	4.8 in

Electrical Ratings

Current / Amperage Rating	15 A
---------------------------	------

Conductor Related

Cable Entry	Plug-In
-------------	---------

Certifications And Compliance

Industry Standard(s)	• CSA Certified • UL Recognized
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Catalog Page - WDK I-15 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - PR205E AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2170_INSTALLINST](#)
- [Literature - Safety Product Guide](#)
- [Literature - Food Processing Guide](#)
- [Literature - Industrial Solutions](#)
- [Sales Drawings - WDK_PR205E_DRAWING_PDF](#)
- [Specifications - PR205E Specification Sheet](#)
- [Specifications - Wiring PR205E specification sheet](#)
- [Specifications - PR205E Specification Sheet French](#)
- [Warranty - Industrial & Commercial Products](#)