

Signal And Control, Panel Safe, 1)
15A 125V GFCI, 1) Cat5E, 1) DB9,
With 3A Circuit Breaker

By Hubbell Wiring Device-Kellems
Catalog # [PR205EDB9B](#)

Signal And Control, Panel Safe, 1) 15A 125V GFCI, 1) Cat5E, 1)
DB9, With 3A Circuit Breaker

Features

- Protective clear cover
- Overcurrent protection
- Finger-safe contacts
- Stainless steel snap latch

Performance

- Electrical - Circuit Breaker - 3A
- Electrical - Data Jack - Cat. 5e
- Electrical - GFCI - Conforms to UL 943 2006 requirement
- Electrical - In-Cabinet Receptacle - GFCI protected
- Environmental - Enclosure - NEMA Type 4, 12 and NEMA Type 4X

General

Catalog Number	PR205EDB9B
Color	Gray, Clear
EU RoHS Indicator	Yes
Enclosure Type	NEMA 12/4
Item Type	Industrial Connectivity
Material	Composite
Material - Mounting Hardware	Screw Mounting
Specifications	• Cover - Clear Polycarbonate (UV Rated) • Finish - Powder Coat • Housing - Cast Aluminum • Latch - Stainless steel
UPC	783585358550

Dimensions



Height	4.9 in
Width	3.6 in

Electrical Ratings

Current / Amperage Rating	15 A
---------------------------	------

Conductor Related

Cable Entry	Plug-In
-------------	---------

Certifications And Compliance

Industry Standard(s)	• CSA Certified • UL Recognized
----------------------	---

Logistics

Carton Quantity	20
-----------------	----

Product Assets

[Catalog Page - WDK I-15 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - PR205EDB9B AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2170_INSTALLINST](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_PR205EDB9B_DRAWING_PDF](#)
[Specifications - Wiring PR205EDB9B specification sheet](#)
[Specifications - PR205EDB9B Specification Sheet](#)
[Specifications - PR205EDB9B Specification Sheet French](#)
[Warranty - Industrial & Commercial Products](#)