

Non-Metallic Raceway, Non-Metallic
PlugTrak Series, PLUGTRAK, 5', 15A
125V, 1-Circuit, Tamper Resistant



By Hubbell Wiring Device-Kellems
Catalog # [PT155112TR](#)

Non-Metallic Raceway, Non-Metallic PlugTrak Series, PLUGTRAK,
5', 15A 125V, 1-Circuit, Tamper Resistant

Features

- Available in 5 ft. or 6 ft. lengths
- Multiple spacing configurations
- Hard wired PlugTrak® mates with LANTrak® fittings and boxes

Performance

- Electrical - Crush Resistance - 300 lbs.
- Electrical - Impact Resistance - 5 ft. lbs
- Electrical - Receptacle Rating - NEMA 5-15R & 5-20R
- Environmental - Flame Rating - UL94V-0
- Environmental - Temperature Range - -25.6° to 158° F
- Mechanical - Wire - #12 AWG Stranded Copper

General

Catalog Number	PT155112TR
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number of Receptacles	5
Series	Non-Metallic
Specifications	• Material - UV Stabilized PVC • Number of Receptacles - 5 Duplex • PlugTrak Amperage - 15A • PlugTrak Length - 5 Foot • Receptacle Face - Thermoplastic • Spacing - 12 Inch
Style	Tamper Resistant
UPC	783585455952

Dimensions

Length	5 ft
--------	------

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating	125 VAC

Conductor Related

Wire Size	#12 AWG THHN
-----------	--------------

Certifications And Compliance

Industry Standard(s)	• CSA Standard C22.2 no. 62 • E118895 / E119190 • UL Standard UL 5A
----------------------	---

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK S-62 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - PT155112TR AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2474_INSTALLINST](#)
[Sales Drawings - WDK_PT155112TR_DRAWING_PDF](#)
[Specifications - PT155112TR Specification Sheet](#)
[Specifications - Wiring PT155112TR Specification Sheet](#)
[Specifications - PT155112TR Specification Sheet French](#)
[Warranty - Industrial & Commercial Products](#)