

Low Voltage Large Capacity Flush  
Furniture Feed Series, 2" EMT  
Though Floor Fitting

By Hubbell Wiring Device-Kellems  
Catalog # [PT2FIT](#)

Fire-Rated Poke-Through Low Voltage Large Capacity Flush  
Furniture Feed Series, 2" EMT Though Floor Fitting

Features

- Single Service Furniture Feed Fitting
- For Use with Power or Data
- Up to 2 Hour Fire Rating
- Step Down Installation
- Cover Flange Sold Separately

Performance

- Electrical - Fire Resistance Rating - 2-Hrs. (D900)
- Electrical - UL Installation - Min. of 2 feet on centers and not more than one unit per 65 sq. ft. of floor area
- Mechanical - Max. Cu Cross Section - 2 in. EMT .0922 sq. in.

General

Catalog Number	PT2FIT
Construction	Fabricated
EU RoHS Indicator	No
Finish Type	Natural
Item Type	3" Fire-Rated Poke-Through Component
Material	Composite
Material - Mounting Hardware	Step-Down Installation
Number Of Outlets	Single Service
Specifications	<ul style="list-style-type: none"><li>• Conduit Cover - 2.47 in. (62.7) and 1.74 in. (44.2) combination knockouts</li><li>• Cored Hole - 3" (76.2) diameter</li></ul>



- Floor Thickness - 2 1/4 in. to 7 in. (57.2 to 177.8)
- Service fitting - Flush aluminum service fitting with epoxy paint finish

Style  
UPC  
In Floor Fitting  
783585498157

Conductor Related

Cable Entry  
Through Cover

Certifications And Compliance

Industry Standard(s)  
cULus Listed

Logistics

Carton Quantity  
Pallet Quantity  
1  
80

Product Assets

[Catalog Page - WDK P-44](#) [Catalog Page - WDK P-33](#) [Catalog Page - WDK P-33](#) [Catalogs - WDK Catalog Full 2024](#) [Engineering Drawing - PT2FIT AutoCAD Drawing](#) [Installation Manuals - WIRING\\_PT2FIT\\_INSTALLINST](#) [Sales Drawings - WDK\\_PT2FIT\\_DRAWING\\_PDF](#) [Specifications - PT2FIT](#) [Specifications - PT2FIT Specification Sheet French](#) [Specifications - PT2FIT Specification Sheet English](#) [Warranty - Industrial & Commercial Products](#)