

2x2 Flush Duplex Series, Complete Unit, Isolated Ground, Black/Brass Finish

By Hubbell Wiring Device-Kellems  
Catalog # [PT2X2IGBRS3](#)

In-Floor Delivery Systems, Fire-Rated Poke-Throughs, 2x2 Flush Duplex Series, Complete Unit, Isolated Ground, Black/Brass Finish

General

Application - For Use On	Carpet
Catalog Number	PT2X2IGBRS3
EU RoHS Indicator	No
Finish Type	Black/Brass
Item Type	3" Fire-Rated Poke Through Component
Knockouts	Duplex Flip Covers
Material - Mounting Hardware	Step-Down Installation
Number Of Outlets	(1) Prewired 20A Duplex IG Receptacle; (2) Installed Cat 6 Jacks
Specifications	<ul style="list-style-type: none"><li>Approval - Approved for use in the City of Chicago</li><li>Cover and flange - Flush thermoplastic cover with painted aluminum flange</li><li>Floor thickness - 2 1/4 to 7 in. (57.2 to 177.8)</li><li>Mounting - 3 in. (76.2) cored concrete diameter through</li></ul>



Style	hole
UPC	FRPT - Complete Kits 783585532011

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>cULus Listed</li><li>Meets ADA Standards</li><li>UL 514A Listed</li></ul>
----------------------	---

Product Assets

- [Catalog Page - WDK P-31 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - PT2X2IGBRS3 AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD1936\\_INSTALLINST](#)
- [Literature - Delivery Systems Product Guide](#)
- [Sales Drawings - WDK\\_PT2X2IGBRS3\\_DRAWINGS\\_PDF](#)
- [Specifications - PT2X2IGBRS3](#)
- [Specifications - PT2X2IGBRS3 Specification Sheet French](#)
- [Specifications - PT2X2IGBRS3 Specification Sheet English](#)
- [Warranty - Industrial & Commercial Products](#)