

2x2 Flush Duplex Series, Complete Unit, Isolated Ground, Gray

By Hubbell Wiring Device-Kellems
Catalog # [PT2X2IGGY](#)

In-Floor Delivery Systems, Fire-Rated Poke-Throughs, 2x2 Flush Duplex Series, Complete Unit, Isolated Ground, Gray

General

Application - For Use On	Carpet
Catalog Number	PT2X2IGGY
EU RoHS Indicator	No
Finish Type	Gray
Item Type	3" Fire-Rated Poke Through Component
Knockouts	Duplex Flip Covers
Material - Mounting Hardware	Step-Down Installation
Number Of Outlets	(1) Prewired 20A Duplex IG Receptacle; (2) Installed Cat 6 Jacks
Specifications	<ul style="list-style-type: none">• Approval - Approved for use in the City of Chicago• Cover and flange - Flush thermoplastic cover with painted aluminum flange• Floor thickness - 2 1/4 to 7 in. (57.2 to 177.8)• Mounting - 3 in. (76.2) cored concrete diameter through



Style	hole
UPC	FRPT - Complete Kits 783585531892

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• cULus Listed• Meets ADA Standards• UL 514A Listed
----------------------	---

Product Assets

- [Catalog Page - WDK P-31 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - PT2X2IGGY AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1936_INSTALLINST](#)
- [Literature - Delivery Systems Product Guide](#)
- [Sales Drawings - WDK_PT2X2IGGY_DRAWINGS_PDF](#)
- [Specifications - PT2X2IGGY](#)
- [Specifications - PT2X2IGGY Specification Sheet English](#)
- [Specifications - PT2X2IGGY Specification Sheet French](#)
- [Warranty - Industrial & Commercial Products](#)