

Complete Unit With 20A Duplex,
(2) 1/2" Diameter Holes for Low
Voltage Wiring, Black/Brass Finish

By Hubbell Wiring Device-Kellems
Catalog # [PT7FSDBRS3A](#)

In-Floor Delivery Systems, Fire-Rated Poke-Throughs, Flush
Duplex Series, Complete Unit With 20A Duplex, (2) 1/2"
Diameter Holes for Low Voltage Wiring, Black/Brass Finish

General

Application - For Use On	Carpet
Catalog Number	PT7FSDBRS3A
EU RoHS Indicator	No
Finish Type	Black/Brass
Item Type	3" Fire-Rated Poke Through Component
Knockouts	Duplex Flip Covers and (2) 1/2" Diameter Holes for Low Voltage Wiring
Material - Mounting Hardware	Step-Down Installation
Number Of Outlets	(1) 20A Duplex Receptacle and (2) 1/2" Diameter Holes for Low Voltage Wiring
Specifications	- Cover Material - Brass cover and flange - Floor thickness - 2 1/4 to 7 in. (57.2 to 177.8) - Mounting - 3 in. (76.2) cored concrete diameter through hole



Style	FRPT - Complete Kits
UPC	783585494173

Certifications And Compliance

Industry Standard(s)	- cULus Listed - Meets ADA Standards - UL 514A Listed
----------------------	---

Product Assets

- [Catalog Page - WDK P-32 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - PT7FSDBRS3A AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1962_INSTALLINST](#)
- [Literature - Delivery Systems Product Guide](#)
- [Sales Drawings - WDK_PT7FSDB_DRAWING_PDF](#)
- [Specifications - PT7FSDBRS3A](#)
- [Specifications - PT7FSDBRS3A Specification Sheet English](#)
- [Specifications - PT7FSDBRS3A Specification Sheet French](#)
- [Warranty - Industrial & Commercial Products](#)